

Evaporation Materials: Oxides

Our evaporation materials are available as granules with size from 1mm, pellets with diameter from 5mm, targets with size up to 1,000mm. They are suitable for both electron- and ion-beam evaporation as well as ion beam sputtering. The parameters in the table below are approximate and depend on the sinter and application conditions.

material	Al_2O_3 aluminium oxide	CeO_2 cerium oxide	HfO_2 hafnium oxide	In_2O_3 indium oxide	$\text{In}_2\text{O}_3\text{-CeO}_2$ indium-cer oxide
density colour transmission	3.9g/cm ³ white 190nm...7μm	7.3g/cm ³ yellow 400nm...12.5μm	9.7g/cm ³ white 190nm...7μm	7.2g/cm ³ yellow 400nm...7μm	7.0g/cm ³ yellow 300nm...12.5μm
refractive index and transmission					
wavelength					
140nm	-	-	-	-	-
150nm	-	-	-	-	-
190nm	1.92	-	2.48	-	-
300nm	1.81	-	2.20	-	-
400nm	1.79	2.23	2.16	2.06	2.06
600nm	1.77	2.20	2.11	1.89	1.89
800nm	1.76	2.18	2.09	1.77	1.77
1μm	1.76	2.18	2.08	1.64	1.64
2μm	1.74	2.17	2.06	-	-
4μm	1.68	2.15	2.02	-	-
7μm	1.47	2.05	1.90	-	-
8μm	-	2.01	-	-	-
10μm	-	1.95	-	-	-
12.5μm	-	1.90	-	-	-
15μm	-	-	-	-	-
transmission range					
standard form and size (other forms and sizes are available by request)	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm
price	150 EUR/kg	190 EUR/kg	710 EUR/kg	870 EUR/kg	1,230 EUR/kg

recommended crystalline quartz deposition monitors:

- with aluminium as electrode material (choice 1)
- with silver as electrode material (choice 2)

Evaporation Materials: Oxides

Our evaporation materials are available as granules with size from 1mm, pellets with diameter from 5mm, targets with size up to 1,000mm. They are suitable for both electron- and ion-beam evaporation as well as ion beam sputtering. The parameters in the table below are approximate and depend on the sinter and application conditions.

material	In ₂ O ₃ -SnO ₂ indium-tin oxide	MgO magnesium oxide	Nb ₂ O ₅ niobium oxide	SiO silicon monoxide	Si ₂ O ₃ disilicon trioxide
density colour transmission	7.1g/cm ³ yellow-green 400nm...1μm	3.6g/cm ³ white 300nm...8μm	4.5g/cm ³ white 400nm...7μm	2.1g/cm ³ dark 800nm...8μm	2.2g/cm ³ gray 300nm...7μm

refractive index and transmission

wavelength					
	transmission range				
140nm	-				-
150nm	-				-
190nm	-				-
300nm	-		1.80	-	-
400nm	2.06		1.76	2.54	-
600nm	1.89		1.74	2.33	-
800nm	1.77		1.73	2.28	1.93
1µm	1.64		1.72	2.26	1.90
2µm	-		1.70	2.24	1.86
4µm	-		1.67	2.20	1.80
7µm	-		1.64	2.10	1.60
8µm	-		1.61	-	1.16
10µm	-		-	-	-
12.5µm	-		-	-	-
15µm	-		-	-	-
standard form and size (other forms and sizes are available by request)	dia 18 x 10mm granules 1-6mm				
price	930 EUR/kg	282 EUR/kg	260 EUR/kg	76 EUR/kg	130 EUR/kg

recommended crystalline quartz deposition monitors:

- with aluminium as electrode material (choice 1)
 - with silver as electrode material (choice 2)

Evaporation Materials: Oxides

Our evaporation materials are available as granules with size from 1mm, pellets with diameter from 5mm, targets with size up to 1,000mm. They are suitable for both electron- and ion-beam evaporation as well as ion beam sputtering. The parameters in the table below are approximate and depend on the sinter and application conditions.

material	SiO_2 silicon dioxide	Sb_2O_3 antimony trioxide	TaO_2 tantalum dioxide	Ta_2O_5 tantalum pentoxide
density colour transmission	2.3g/cm ³ white 190nm...2μm	5.2g/cm ³ white 400nm...12.5μm	8.2g/cm ³ dark gray 300nm...7μm	8.2g/cm ³ white 300nm...7μm
refractive index and transmission				
wavelength				
140nm	-	-	-	-
150nm	-	-	-	-
190nm	1.56	-	-	-
300nm	1.49	-	-	-
400nm	1.47	2.15	2.34	2.34
600nm	1.46	2.09	2.25	2.25
800nm	1.45	2.06	2.14	2.14
1μm	1.45	2.04	2.10	2.10
2μm	1.44	2.00	2.08	2.08
4μm	-	1.95	2.04	2.04
7μm	-	1.89	1.99	1.99
8μm	-	1.80	1.77	1.77
10μm	-	1.69	-	-
12.5μm	-	1.55	-	-
15μm	-	-	-	-
standard form and size (other forms and sizes are available by request)	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm
price	60 EUR/kg	by request	810 EUR/kg	730 EUR/kg

recommended crystalline quartz deposition monitors:

- with aluminium as electrode material (choice 1)
- with silver as electrode material (choice 2)

Evaporation Materials: Oxides

Our evaporation materials are available as granules with size from 1mm, pellets with diameter from 5mm, targets with size up to 1,000mm. They are suitable for both electron- and ion-beam evaporation as well as ion beam sputtering. The parameters in the table below are approximate and depend on the sinter and application conditions.

material	TiO titanium monoxide	Ti ₂ O ₃ ditanium trioxide	Ti ₃ O ₅ trititanium pentoxide	TiO ₂ titanium dioxide	Y ₂ O ₃ yttrium oxide
density colour transmission	4.9g/cm ³ gold 400nm...10µm	4.6g/cm ³ violet 400nm...10µm	4.6g/cm ³ dark violet 400nm...10µm	4.2g/cm ³ white 400nm...10µm	5.0g/cm ³ white 300nm...8µm

refractive index and transmission

wavelength	TiO titanium monoxide	Ti ₂ O ₃ ditanium trioxide	Ti ₃ O ₅ trititanium pentoxide	TiO ₂ titanium dioxide	Y ₂ O ₃ yttrium oxide
140nm	-	-	-	-	-
150nm	-	-	-	-	-
190nm	-	-	-	-	-
300nm	-	-	-	-	-
400nm	2.68	2.68	2.68	2.68	2.07
600nm	2.60	2.60	2.60	2.60	1.98
800nm	2.52	2.52	2.52	2.52	1.93
1µm	2.49	2.49	2.49	2.49	1.91
2µm	2.41	2.41	2.41	2.41	1.90
4µm	2.31	2.31	2.31	2.31	1.89
7µm	2.02	2.02	2.02	2.02	1.86
8µm	1.87	1.87	1.87	1.87	1.78
10µm	1.39	1.39	1.39	1.39	1.74
12.5µm	-	-	-	-	-
15µm	-	-	-	-	-
standard form and size (other forms and sizes are available by request)	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm
price	170 EUR/kg	150 EUR/kg	150 EUR/kg	100 EUR/kg	280 EUR/kg

recommended crystalline quartz deposition monitors:

- with aluminium as electrode material (choice 1)
- with silver as electrode material (choice 2)

Evaporation Materials: Oxides

Our evaporation materials are available as granules with size from 1mm, pellets with diameter from 5mm, targets with size up to 1,000mm. They are suitable for both electron- and ion-beam evaporation as well as ion beam sputtering. The parameters in the table below are approximate and depend on the sinter and application conditions.

material	Yb_2O_3 ytterbium oxide	ZrO_2 zirconium oxide
density colour transmission	9.2g/cm ³ white 400nm...8μm	5.6g/cm ³ white 300nm...7μm
refractive index and transmission		
wavelength		
140nm	-	-
150nm	-	-
190nm	-	-
300nm	-	2.25
400nm	1.98	2.22
600nm	1.95	2.16
800nm	1.92	2.14
1μm	1.90	2.12
2μm	1.88	2.10
4μm	1.86	2.05
7μm	1.78	1.96
8μm	1.74	-
10μm	-	-
12.5μm	-	-
15μm	-	-
standard form and size (other forms and sizes are available by request)	dia 18 x 10mm granules 1-6mm	dia 18 x 10mm granules 1-6mm
price	300 EUR/kg	100 EUR/kg